

6 ft USB VGA Adapter Cable - External Multi Monitor Video M/M

Produkt ID: USB2VGAMM6



The USB2VGAMM6 External USB VGA Adapter Cable offers a hassle-free multi-monitor solution, turning a USB 2.0 port into a VGA video connection. This 6-foot USB Display Adapter is a complete solution, ready to go out of the box with all the cables you need built right onto the adapter. Simply install the drivers, connect to your computer and display. Built-on cables make the USB2VGAMM6 easier to install and does away with the need to worry about forgetting a cable.

Instead of having to open the computer case to install a specialized video card to accommodate a multi-display configuration, USB2VGAMM6 functions as an external USB video card saving both time and hassle.

Multiple (USB2VGAMM6) adapters (up to 5 total) can be used on a single system to provide several mirrored displays or extended desktops - a convenient and cost-effective multi-VGA option for virtually any laptop or desktop operating environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Extend or mirror the image shown on an existing laptop or desktop display
- Run multiple applications on different screens, check your email on one display and work on a document in the other.

Funktioner

- Optimal performance at 1680x1050 and ideal for use with 20" to 22" monitors or smaller
- Built-on USB and VGA cables
- Hassle-free installation
- No power adapter required

Hårdvara

Garantipolicy	2 Years
AV-ingång	USB 2.0
AV-utgång	VGA
USB-passthrough	Nej
Minne	16MB
Chipset-ID	DisplayLink - DL-165

Prestanda

Maximal analog upplösning	1600x1200(standard) or 1680x1050(wide) @ 32 bits
Stödda upplösningar	Widescreen (16/32 bit): 1680x1050, 1440x900, 1366x768 Standard (16/32 bit): 1600x1200, 1280x1024, 1024x768, 800x600, 640x480
Allmänna specifikationer	This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger or Fresco family chipset.
Medeltid mellan fel (MTBF)	59,000 hours

Kontakt(er)

Kontakttyp(er)	USB Type-A (4-stifts) USB 2.0
----------------	-------------------------------

VGA (15-stifts, High Density D-Sub)

Mjukvara

OS-kompatibilitet	Windows® 10 (32/64), 8/8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64)
	macOS Monterey (12.0), Big Sur (11.0) El Capitan (10.11), Yosemite (10.10), Mavericks (10.9) Mountain Lion (10.8), Lion (10.7), Snow Leopard (10.6)
	Ubuntu 16.04, 14.04

Särskilda
anmärkningar/krav

System- och kabelkrav	System Processor: 1.2GHz
	System Memory: 512MB
Obs.	This USB video adapter uses a DisplayLink® family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic®
	Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources
	This USB video adapter is not intended for graphical intensive applications, such as gaming

Utseende

Färg	Svart
Kabellängd	6.0 ft [1.8 m]
Produktlängd	6.0 ft [1.8 m]
Produktbredd	1.9 in [48 mm]
Produkt höjd	0.9 in [23.5 mm]
Produktvikt	3.5 oz [100 g]

Förpackning

Package Length	6.5 in [16.6 cm]
Package Width	2.5 in [63 mm]



Package Height 5.6 in [14.3 cm]

Fraktvikt (förpackning) 10.9 oz [310 g]

Vad det är i lådan

Ingår i paketet USB to VGA Adapter

Driver CD

Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

