

Professional USB to VGA External Dual or Multi Monitor Video Adapter

Produkt ID: USB2VGAPRO



The USB2VGAPRO Professional USB VGA External Dual or Multi Monitor Video Adapter is the perfect solution for turning your workstation into a dual or multi-monitor environment using your USB ports - providing high quality, dual display or multi-monitor capability for a variety of laptop or desktop applications.

With improved performance compared to our USB2VGA and USB2VGA2, this USB VGA display adapter is capable of running up to five additional displays from one computer simultaneously (using four USB2VGAPRO External Multi Monitor Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external VGA video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

USB2VGAPRO offers support for Microsoft Windows® (including Aero themes) and Mac OS X, and with support for resolutions up to 1920x1200 this device is ideal for larger displays / monitors.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Can't install a new or additional video card? No problem, the USB2VGAPRO uses USB ports to add VGA connectivity to your PC or Mac
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGAPRO device for each additional display

- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different screens; check your email on one display while editing a document on the other
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Funktioner

- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- Connect up to five adapters to one PC for a true extended desktop experience
- USB Powered - No external power adapter required
- Works with Mac OS X
- Support for Aero themes in Windows®
- Quick and easy install

Hårdvara

Garantipolicy	2 Years
AV-ingång	USB 2.0
AV-utgång	VGA
USB-passthrough	Nej
Minne	16MB
Chipset-ID	DisplayLink - DL-195

Prestanda

Maximal analog upplösning	1920x1200 (32-bit Color)
Stödda upplösningar	Standard(16/32 bit): 640x480, 800x600, 1280x1024, 1024x768, 1600x1200



Widescreen(16/32 bit):

1366x768, 1440X900, 1680x1050, 1920x1280, 1920x1200

Stöd för widescreen Ja

Kontakt(er)

Kontakttyp(er) VGA (15-stifts, High Density D-Sub)

USB Type-A (4-stifts) USB 2.0

Mjukvara

OS-kompatibilitet Windows® 2000, XP, Vista, 7, 8/8.1, 10
 macOS 10.6 - 10.11, 11.0
 Chrome OS v51
 Ubuntu 14.04, 16.04, 18.04

Särskilda
anmärkningar/
krav

System- och kabelkrav System Processor: 1.2GHz

System Memory: 512MB

Obs. Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported

This USB video adapter uses a DisplayLink® family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic®

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming


Indikatorer

LED-indikatorer Blue - Power

Utseende

Färg Svart

Produktlängd 3.5 in [90 mm]



Produktbredd	1.9 in [48 mm]
Produkt höjd	0.9 in [23.5 mm]
Produktvikt	2.6 oz [73 g]

Förpackning

Package Length	6.4 in [16.3 cm]
Package Width	2.5 in [62.5 mm]
Package Height	5.7 in [14.4 cm]
Fraktvikt (förpackning)	8.8 oz [250 g]

Vad det är i lådan

Ingår i paketet	Driver CD
	Instruction Manual
	USB to VGA Adapter

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

