

USB 3.0 to Gigabit Ethernet Adapter NIC w/ USB Port - White

Product ID: USB31000SPTW



The USB31000SPTW USB 3.0 to Gigabit Ethernet Adapter lets you add a Gigabit network port to your Macbook or Ultrabook computer through a USB 3.0 port, and features an integrated USB 3.0 pass-through port that keeps your USB port available for use with other peripherals. The RJ45 port supports 10/100/1000 Mbps Ethernet and is fully compatible with IEEE 802.3i/u/ab standards.

An ideal replacement LAN adapter or laptop accessory, this compact USB 3.0 NIC leverages the 5 Gbps speed of USB 3.0 to provide full gigabit bandwidth and also offers backward compatibility with USB 2.0 systems (speed limited by USB bus).

The adapter supports features such as IPv4/IPv6 packet Checksum Offload Engine (COE) and TCP large send offload to reduce the load on your CPU. Jumbo Frames, full-duplex operation with 802.3x flow control and VLAN tagging are also supported, making this an efficient and full-featured USB network adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Replacement for a failed built-in Gigabit Ethernet port on a laptop
- Add Gigabit Ethernet capabilities to a desktop or laptop

Features

- Integrated USB 3.0 pass-through port
- IEEE 802.3, 802.3u and 802.3ab (10BASE-T, 100BASE-TX, and 1000BASE-T) compatible
- Crossover Detection & Auto-Correction (Auto MDIX)
- IEEE 802.1Q VLAN Tagging support
- Up to 4K Jumbo Frame support
- Supports Checksum Offload (IPv4, IPv6, TCP, UDP) and Large Send Offload
- Compact, lightweight design for maximum portability
- Gigabit Ethernet port through a USB 3.0 / 2.0 connection

Hardware	Warranty	2 Years
	Ports	1
	Interface	RJ45 (Gigabit Ethernet)
	Bus Type	USB 3.0
	USB Pass-Through	Yes
	Industry Standards	IEEE802.3i, IEEE 802.3u, IEEE 802.3ab, IEEE 802.3az
	Chipset ID	ASIX - AX88179 VIA/VLI - VL811
Performance	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet - Full-Duplex)
	Max Distance	100 m / 330 ft
	Type and Rate	USB 3.0 - 5 Gbit/s
	Compatible Networks	10/100/1000 Mbps
	Auto MDIX	Yes
	Full Duplex Support	Yes
	Jumbo Frame Support	4K max.
	Connector(s)	Connector Type(s)
Connector Type(s)		USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector Type(s)		USB Type-A (9 pin) USB 3.0 (5 Gbps)
Software	OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 Mac OS 10.6 to 10.15 - <i>VLAN tagging is currently not supported in Mac OS</i>

Linux Kernel 2.6.25 to 4.11.x <i>LTS Versions only</i>

Special Notes / Requirements	System and Cable Requirements	Available USB Port
Indicators	LED Indicators	10/100 Link/Activity (Green)
	LED Indicators	Gigabit Link/Activity (Amber)
Power	Power Source	USB-Powered
Environmental	Operating Temperature	0C to 50C (32F to 122F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	5~85% RH
Physical Characteristics	Color	White
	Form Factor	Attached Cable
	Material	Plastic
	Cable Length	6.1 in [1.6 cm]
	Product Length	5.0 in [1.3 cm]
	Product Width	1.4 in [35 mm]
	Product Height	0.7 in [17 mm]
	Weight of Product	1.6 oz [44 g]
Packaging Information	Package Length	5.6 in [1.4 cm]
	Package Width	6.7 in [1.7 cm]
	Package Height	1.1 in [29 mm]
	Shipping (Package) Weight	4.7 oz [132 g]
What's in the Box	Included in Package	Instruction Manual
	Included in Package	Driver CD
	Included in Package	USB 3.0 Network Adapter

**Product appearance and specifications are subject to change without notice.*