

USB to USB-C Cable - M/M - 1 m (3 ft.) - USB 3.0 - USB-A to USB-C

Product ID: USB315AC1M



This USB to USB-C cable lets you connect your USB 3.0, USB Type-C devices such as a hard drive, or mobile device to the USB Type-A port on your computer, charger or tablet.

The USB315AC1M from StarTech.com comes with a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility

Applications

- Connect USB-C peripherals, such as a hard drive, to your USB-A laptop or tablet
- Charge your USB-C mobile device from a USB-A laptop or wall charger
- Sync your USB-C mobile device with a USB-A computer

Features

- Supports data transfer rates up to 5Gbps
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel

Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-C (24 pin) USB 3.0 (5Gbps)

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/32 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.6 in [16.0 mm]
Product Height	0.3 in [8.0 mm]
Weight of Product	1.4 oz [41.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.7 oz [49.0 g]



**What's in the
Box**

Included in Package	USB-C to USB-A cable
---------------------	----------------------

****Product appearance and specifications are subject to change without notice.***

