

USB-C to USB-A Adapter, Right-Angled, USB 5Gbps, 3A, USB-C Male to USB-A Female Converter, Durable Metal Housing - Thunderbolt Compatible

**Product ID:** USB31CAADGCPRA



Connect a USB-A device to a USB-C laptop or convert a USB-A cable to Type-C, using this compact USB-C to USB-A Male to Female adapter. The connector markings enable quick visual identification, distinguishing this adapter from other similar-looking or unmarked USB-C adapters. Eliminate guesswork and always choose the appropriate adapter that supports USB 5Gbps.

The USB-C to USB-A adapter is universally compatible with any Operating System. Simple plug-and-play setup enables instant deployment. The adapter supports USB 5Gbps and USB 2.0 (480Mbps), and facilitates up to 5V/3A output from a powered USB-C connection such as a wall charger. This enables up to 15W charging to a USB-A device from a USB-C source. Please note that USB-C video and Power Delivery are not supported.

The USB C to A adapter has a durable aluminum alloy housing that protects against wear and tear. The nickel-plated connectors are designed for long-lasting reliability and performance.

## Certifications, Reports and Compatibility



## Applications

- Right angled connector reduces cable strain in tight spaces
- Charge a USB-C device with up to 15W from a powered USB-A connection
- Slim, compact housing is durable and will not obstruct adjacent ports

## Features

- **RIGHT ANGLED USB-C ADAPTER:** Compact Right Angled USB-C Male to USB-A Female adapter connects neatly to a USB-C host; Ideal for installations where space is limited; Clear connector markings with data/power specs enable easy identification at a glance
- **QUALITY CONSTRUCTION:** Aluminum alloy outer housing enhances durability and wear protection; Slim design prevents the obstruction of adjacent device ports; Durable Nickel-plated connectors ensure consistent data throughput
- **COMPATIBILITY:** Versatile compatibility with USB-A cables and devices; Supports USB-C laptops and portable devices; Charge a portable USB-C device from a USB-A charger (up to 15W); NOTE: Please confirm compatibility between the USB-A device and USB-C host
- **QUICK INSTALLATION:** Ideal for mounted devices with bottom or rear-facing ports; Right-angled connector reduces cable and port strain from bending; Plug-and-play design requires no drivers for a hassle-free setup; Compatible with any Operating System
- **RELIABLE TRANSMISSION:** USB-C to USB-A adapter supports 5Gbps data transfer; Backward compatibility with USB 480Mbps (USB 2.0) for legacy devices; Supports up to 5V/3A output from a USB-A charger; NOTE: USB-C video and Power Delivery are not supported

---

### Hardware

Warranty	2 Years
Active or Passive Adapter	Passive
Ports	1
Connector Plating	Nickel

---

### Performance

Maximum Data Transfer Rate	5Gbps
----------------------------	-------

---

### Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
Connector B	1 - USB Type-A (9 pin, 5 Gbps)

---

### Power

Input Voltage	5V DC
Input Current	3A

---

### Environmental

Operating Temperature	0 to 40 (32&degF to 104&degF)
-----------------------	-------------------------------

Storage Temperature	-10 to 70 (14&degF to 158&degF)
Humidity	10%~90%

---

#### Physical Characteristics

Color	Black
Connector Style	Right Angled
Material	Aluminum
Product Length	1.0 in [2.6 cm]
Product Width	0.6 in [1.4 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	0.2 oz [5.0 g]

---

#### Packaging Information

Package Length	3.9 in [10.0 cm]
Package Width	3.5 in [8.9 cm]
Package Height	0.4 in [9.0 mm]
Shipping (Package) Weight	0.4 oz [10.0 g]

---

#### What's in the Box

Included in Package	1 - USB-C to Right Angle USB-A Adapter - M/F
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***