

3ft (1m) USB C Cable 10Gbps - USB-IF Certified USB-C Cable - USB 3.1 Type-C Cable - 100W (5A) Power Delivery Charging, DP Alt Mode - USB C to C Cord - Charge & Sync

**Product ID:** USB31CCV1M



This USB 3.2 Gen 2 10Gbps USB-C cable lets you connect your USB Type-C devices for syncing, charging and powering your devices.

The cable is also compatible with Thunderbolt 3 ports, which means you can charge and sync your USB-C mobile devices using your Thunderbolt 3 laptop.

#### Power your USB-C devices

With up to 5A (100W) of power delivery, you can power a USB-C laptop, such as your Apple MacBook or Microsoft Surface Book. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

You can use this USB Type-C cable to power your USB-C hard drive from the USB-C port on your laptop.

#### Charge your mobile devices

When used with devices that support PD 3.0, this cable charges up to 20V and 5A for a maximum of 100W. It can decrease your charge time and make sure your mobile devices are ready, whenever you need them.

#### Deliver 8K Video with DisplayPort 1.4 Alt Mode

The cable supports 8K 30Hz video with DisplayPort 1.4 and is backward compatible to connect your docking station or laptop to a monitor that supports 4K or 1080p resolutions.

#### Provide superior connections with USB-IF certified cables

The cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 3.2 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable, high-quality cable for all your USB-C devices.

The USB31CCV1M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

## Features

- **HIGH PERFORMANCE:** 3.3ft (1m) Certified USB-C cable supports SuperSpeed USB 3.2 Gen 2 (10Gbps) data transfer; DisplayPort 1.4 Alt mode up to 8K 30Hz; USB C to C cable supports up to 100W (5A) Power Delivery 3.0 charging; Thunderbolt 3 compatible
- **USB-IF CERTIFIED USB C CABLE:** For home or office, this high quality USB C Cord has been tested to meet USB 3.2 Gen 2 standards; 32 AWG conductors with Al-Mylar foil (85% Braid coverage) EMI shielding provides superior signal integrity and reliability
- **DURABLE DESIGN:** USB Type-C cable has been tested to withstand 10,000+ insertions & 4000+ bend angle of +/- 60 Long lasting flexible TPE jacket and strain relief; TPE is non-toxic and halogen free; Compatible with USB 3.2 and earlier versions
- **APPLICATIONS:** Works w/docking stations/external hard drives; TB3/4 or USB-C laptops MacBook Air/Pro, Surface Book, X1 Carbon, iPad Pro, iPhone 15 [Plus/Pro/Max] and up, Samsung Galaxy S8 & up, Pixel 5; USB-C portable monitors Asus ZenScreen/ProArt
- **SPECS:** 3.3 feet (1 meter); Color: Black; USB 3.2 Gen 2 10Gbps; PD 3.0, 20V (max), 5A (max); USB C Cable Male to Male; 0.19" (4.8 mm) Outer Diameter, 32 AWG; Jacket: TPE; EMI Shield: Al-Mylar Foil, 85% Braid; DP 1.4 Alt mode 8K 30Hz

---

### Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Maximum Digital Resolutions	8K @ 30Hz
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s

---

## Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)

## Power

Power Delivery	100W
----------------	------

## Physical Characteristics

Color	Gray and Black
Wire Gauge	30/32 AWG
Cable Length	3.3 ft [1 m]
Cable OD	0.2 in [4.8 mm]
Product Length	3.3 ft [1.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [0.7 cm]
Weight of Product	1.6 oz [44.0 g]

## Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	1.7 oz [49.0 g]

## What's in the Box

Included in Package	1 - 1m USB-C 10 Gbps Cable
---------------------	----------------------------

***\*Product appearance and specifications are subject to change without notice.***