

## 1m (3ft) Certified SuperSpeed USB 3.0 A to B Cable - M/M

Produkt ID: USB3CAB1M



The USB3CAB1M 1-meter USB 3.0 A-to-B cable provides a high quality connection between peripheral devices that feature a USB 3.0 type-B port, such as hard drive enclosures, card readers, docking stations and video capture devices and a USB-capable computer.

This cable is USB-IF certified to USB 3.0 specifications, guaranteeing a dependable, long-lasting connection to your USB 'B' devices and is backed by StarTech.com's Lifetime Warranty.

### Certifikat, rapporter och kompatibilitet

#### Användning

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server

#### Funktioner

- 1x USB 'A' male connector
- 1x USB 'B' male connector
- USB-IF Certified SuperSpeed USB 3.0
- Data transfer rates up to 5Gbps
- Aluminum-Mylar Foil with Braided Shielding

- Molded connectors with strain relief
- Backward compatible with USB 2.0

---

#### Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

---

#### Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
-------------------	--------------------

---

#### Kontakt(er)

Connector A	USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9-stifts) USB 3.0

---

#### Miljö

Drifttemperatur	-20°C to 80°C (-4°F to 176°F)
Förvaringstemperatur	-20°C to 80°C (-4°F to 176°F)

---

#### Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	24/28 AWG
Kabellängd	39.4 in [100 cm]
Produktlängd	39.4 in [100.0 cm]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	1.7 oz [49.0 g]

---

#### Förpackning



Förpackningsantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.6 in [16.0 mm]
Fraktvikt (förpackning)	2.0 oz [58.0 g]

---

Vad det är i lådan

Ingår i paketet	1m USB 3.0 Certified A to B Cable - M/M
-----------------	---

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

