

2m (6 ft) Certified SuperSpeed USB 3.0 A to B Cable - M/M

Produkt ID: USB3CAB2M



The USB3CAB2M 2-meter USB 3.0 A-to-B cable provides a high quality connection between peripheral devices that feature a USB 3.0 type-B port, such as hard drive enclosures, card readers, docking stations and video capture devices and a USB-capable computer.

This cable is USB-IF certified to USB 3.0 specifications, guaranteeing a dependable, long-lasting connection to your USB 'B' devices and is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server

Funktioner

- 1x USB 'A' male connector
- 1x USB 'B' male connector
- USB-IF Certified SuperSpeed USB 3.0
- Data transfer rates up to 5Gbps
- Aluminum-Mylar Foil with Braided Shielding

- Molded connectors with strain relief
- Backward compatible with USB 2.0

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
-------------------	--------------------

Kontakt(er)

Connector A	USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9-stifts) USB 3.0

Miljö

Drifttemperatur	-20°C to 80°C (-4°F to 176°F)
Förvaringstemperatur	-20°C to 80°C (-4°F to 176°F)

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	24/28 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.6 ft [2 m]
Produktvikt	3.2 oz [90 g]

Förpackning

Förpackningsantal	1
Package Length	8.7 in [22 cm]



Package Width 7.9 in [20 cm]

Package Height 0.6 in [16 mm]

Fraktvikt (förpackning) 3.5 oz [99 g]

Vad det är i lådan

Ingår i paketet 2m USB 3.0 Certified A to B Cable - M/M

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

