

1m (3ft) Certified SuperSpeed USB 3.0 (5Gbps) A to Micro B Cable - M/M

Produkt ID: USB3CAUB1M



The USB3CAUB1M 1m USB 3.2 Gen 1 Micro B cable provides a high quality connection between your Micro USB-equipped USB 3.2 Gen 1 devices (e.g. card reader, video capture device, hard drive enclosure, etc.) and a USB-capable computer.

This cable is USB-IF certified to USB 3.2 Gen 1 specifications, guaranteeing a dependable, long-lasting connection to your Micro USB devices and is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Transfer data, connect to various USB devices, and provide power while charging your Micro USB device

Funktioner

- 1x USB 'A' male connector
- 1x USB Micro-B male connector
- USB-IF Certified SuperSpeed USB 3.2 Gen1

- Supports high-speed data transfer rates of up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
-------------------	--------------------

Kontakt(er)

Connector A	1 - USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	1 - USB 3.0 Micro-B (10-stifts, SuperSpeed)

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	24/28 AWG
Kabellängd	3.3 ft [1 m]
Produktlängd	3.3 ft [1.0 m]
Produktbredd	5.9 in [15.0 cm]
Produkthöjd	2.0 in [5.0 cm]
Produktvikt	1.7 oz [49.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	7.6 in [19.4 cm]

Paketets bredd	7.8 in [19.8 cm]
Paketets höjd	0.7 in [1.7 cm]
Fraktvikt (förpackning)	2.1 oz [60.0 g]

Vad det är i lådan

Ingår i paketet	1 - 1m SuperSpeed USB 3.0 Certified A to Micro B Cable - M/M
-----------------	--

Warranty
Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.