

6 ft SuperSpeed USB 3.0 Cable A to A - M/M

**Product ID:** USB3SAA6



StarTech.com's 6ft SuperSpeed USB 3.0 cable (A-A) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, this USB 3.0 A to A Male/Male cable provides connectivity between a PC and hub or other USB A devices, delivering a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.0 A to A device cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.0 device cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

## Certifications, Reports and Compatibility

## Applications

- Connect a USB 3.0 SuperSpeed A devices such as a USB hub to a Desktop or Server

## Features

- Cable and Connectors are compliant with USB 3.0 SuperSpeed specifications

---

### Hardware

Warranty

Lifetime

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Foil shielded twisted pair

**Performance**

Type and Rate USB 3.0 - 5 Gbit/s

**Connector(s)**

Connector A USB Type-A (9 pin) USB 3.0 (5 Gbps)

Connector B USB Type-A (9 pin) USB 3.0 (5 Gbps)

**Physical Characteristics**

Color Blue

Wire Gauge 28 AWG

Cable Length 6.0 ft [1.8 m]

Product Length 6.0 ft [1.8 m]

Product Width 0.0 in [0.0 mm]

Product Height 0.0 in [0.0 mm]

Weight of Product 2.5 oz [71.0 g]

**Packaging Information**

Package Length 8.7 in [22.0 cm]

Package Width 7.9 in [20.0 cm]

Package Height 0.7 in [17.0 mm]

Shipping (Package) Weight 2.8 oz [80.0 g]

**What's in the Box**

Included in Package USB A to A Male to Male cable

***\*Product appearance and specifications are subject to change without notice.***

