

10 ft SuperSpeed USB 3.0 Cable A to B - M/M

Productcode: USB3SAB10



StarTech.com's 10ft USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 10ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 10ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 10ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certificaties, rapporten en compatibiliteit



Toepassingen

Eigenschappen

- Cable and Connectors are compliant with USB 3.0 SuperSpeed specifications

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Folie afgeschermd getwist paar

Prestaties

Type en snelheid	USB 3.0 - 5 Gbit/s
------------------	--------------------

Connector(en)

Connector A	1 - USB Type-A (9-polig) USB 3.0 (5 Gbps)
Connector B	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Fysieke eigenschappen

Kleur	Blauw
Draaddikte	28 AWG
Kabellengte	10.0 ft [3.0 m]
Lengte product	10.0 ft [3.0 m]
Breedte product	0.0 in [0.0 cm]
Hoogte product	0.0 in [0.0 cm]
Gewicht product	4.9 oz [137.4 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	4.3 in [11.0 cm]
Package Width	1.1 in [28.0 mm]
Package Height	8.4 in [21.4 cm]
Verzendgewicht (verpakt)	5.0 oz [142.1 g]

Wat wordt er

meegeleverd

Meegeleverd

1 - 10 ft SuperSpeed USB 3.0 Cable A to B - M/M

Garantiebepalinge
n

Warranty

Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.