

10 ft Black SuperSpeed USB 3.0 Cable A to B - M/M

**Product ID:** USB3SAB10BK



StarTech.com's 10ft Black SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 10ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 10ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 10ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

## Certifications, Reports and Compatibility

## Applications

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

## Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Molded connectors with strain relief

---

### Hardware

Warranty

Lifetime

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Foil shielded twisted pair

---

**Performance**

Type and Rate USB 3.0 - 5 Gbit/s

---

**Connector(s)**

Connector A USB Type-A (9 pin) USB 3.0 (5 Gbps)

Connector B USB Type-B (9 pin) USB 3.0

---

**Environmental**

Operating Temperature -10C to 50C (14F to 122F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0~75% RH

---

**Physical Characteristics**

Color Black

Wire Gauge 28 AWG

Cable Length 10.0 ft [3.0 m]

Product Length 10.0 ft [3.0 m]

Product Width 0.5 in [13.5 mm]

Product Height 0.5 in [11.5 mm]

Weight of Product 4.6 oz [129.7 g]

---

**Packaging Information**

Package Length 0.0 in [0.1 mm]

Package Width 7.9 in [20.0 cm]

Package Height 8.7 in [22.0 cm]

Shipping (Package) Weight 4.9 oz [137.7 g]

---

**What's in the**



**Box**

Included in Package      10ft black USB 3.0 A to B cable

---

***\*Product appearance and specifications are subject to change without notice.***

