

1 ft SuperSpeed USB 3.0 (5Gbps) Cable A to B - M/M

Productcode: USB3SAB1



StarTech.com's 1-foot USB 3.2 Gen 1 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the 1-foot USB 3.2 Gen 1 cable supports a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 1-foot USB 3.2 Gen 1 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 1ft USB 3.2 Gen 1 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Connect a SuperSpeed USB 3.0 device (Hubs, external storage device) to an USB 3.0 capable PC, laptop, or Server

Eigenschappen

- Shielded Twisted Pair (STP) design which prevents electro-magnetic interference (EMI)
- Ondersteuning voor dataoverdrachtssnelheden tot 5 Gbps - 10x sneller dan USB 2.0
- Backward compatible with USB 2.0
- Nickel-plated connectors

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Prestaties

Type en snelheid	USB 3.0 - 5 Gbit/s
------------------	--------------------

Connector(en)

Connector A	1 - USB Type-A (9-polig) USB 3.0 (5 Gbps)
Connector B	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Fysieke eigenschappen

Kleur	Blauw
Draaddikte	28 AWG
Kabellengte	1.0 ft [0.3 m]
Lengte product	1.0 ft [0.3 m]
Gewicht product	0.9 oz [26 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.4 in [11 mm]

Verzendgewicht (verpakt)	1.2 oz [35 g]
-----------------------------	---------------

Wat wordt er
meegeleverd

Meegeleverd	1 - 1 ft SuperSpeed USB 3.0 Cable A to B - M/M
-------------	--

Garantiebepalinge
n

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.