

1 ft SuperSpeed USB 3.0 Cable A to B - M/M

**Product ID:** USB3SAB1



StarTech.com's 1-foot USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 1-foot USB 3.0 cable supports a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 1-foot USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 1ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

## **Certifications, Reports and Compatibility**

### **Applications**

- Connect a SuperSpeed USB 3.0 device (Hubs, external storage device) to an USB 3.0 capable PC, laptop, or Server

### **Features**

- Shielded Twisted Pair (STP) design which prevents electro-magnetic interference (EMI)
- Support for data transfer rates up to 5Gbps - 10x faster than USB 2.0
- Backward compatible with USB 2.0
- Nickel-plated connectors

---

**Hardware**

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Performance**

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

---

**Connector(s)**

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9 pin) USB 3.0

---

**Physical Characteristics**

Color	Blue
Wire Gauge	28 AWG
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]
Weight of Product	0.9 oz [26 g]

---

**Packaging Information**

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.4 in [11 mm]
Shipping (Package) Weight	1.2 oz [35 g]

---

**What's in the Box**

Included in Package	1 ft SuperSpeed USB 3.0 Cable A to B - M/M
---------------------	--------------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

