

1m SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB1M



The USB3SAB1M 1m USB 3.0 A-to-B cable allows you to connect your USB 3.0 type-B devices, such as your hard drive enclosures, card readers, docking stations and video capture devices.

The USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, which helps to prevent electro-magnetic interference and ensures reliable data communication.

The 1m cable is backed by StarTech.com's Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop or server

Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Molded connectors with strain relief
- Data transfer rates up to 5Gbps

Hardware	Warranty	Lifetime
	Connector Plating	Nickel

Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	Connector B	USB Type-B (9 pin) USB 3.0
Physical Characteristics	Color	Blue
	Wire Gauge	28 AWG
	Cable Length	39.4 in [10 cm]
	Product Length	39.4 in [10.0 cm]
	Product Width	0.5 in [13.5 mm]
	Product Height	0.5 in [11.5 mm]
	Weight of Product	1.8 oz [52.000 g]
Packaging Information	Package Quantity	1
	Package Length	0.0 in [0.070 mm]
	Package Width	4.9 in [1.2 cm]
	Package Height	8.9 in [2.2 cm]
	Shipping (Package) Weight	2.0 oz [58.000 g]
What's in the Box	Included in Package	1m SuperSpeed USB 3.0 Cable A to B - M/M

**Product appearance and specifications are subject to change without notice.*

