

2m Black SuperSpeed USB 3.0 Cable - Right Angle A to B - M/M

**Product ID:** USB3SAB2MRA



The USB3SAB2MRA 2m Black USB 3.0 A to B cable features a right-angled USB 'A' male connector, enabling you to connect your USB 3.0 Type 'B' peripherals to your PC, laptop, or server, even in hard to reach areas and tight spaces.

The right-angled USB 'A' connector positions the cable nearly flush against a wall or other surface, and eliminates the space typically required to accommodate a 'straight' connection from the cable into the USB port.

Harnessing the full capabilities of the SuperSpeed USB 3.0 standard when used with a USB 3.0 host and device, the 2m cable offers a bandwidth of 5Gbps.

Plus, this right angle USB 3.0 cable also features high quality Shielded Twisted Pair (STP) construction, which helps prevent electro-magnetic interference and ensure reliable data communication.

The USB3SAB2MRA USB 3.0 A to B cable is backed by StarTech.com's Lifetime Warranty, for guaranteed quality and dependability.

## Certifications, Reports and Compatibility

## Applications

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server, even in hard to reach areas and tight spaces

## Features

- 1x Right-angled USB 3.0 'A' male connector

- 1x USB 3.0 'B' male connector
- Designed and constructed to SuperSpeed USB 3.0 Specifications
- High quality Shielded Twisted Pair (STP) construction
- Data transfer rates up to 5Gbps
- Molded connectors with strain relief
- Backward compatible with USB 2.0

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Foil shielded twisted pair

---

#### Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

---

#### Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9 pin) USB 3.0

---

#### Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	28 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2 m]
Product Width	0.4 in [11 mm]
Product Height	0.6 in [14 mm]
Weight of Product	3.0 oz [84 g]

---

#### Packaging



**Information**

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	3.2 oz [92 g]

---

**What's in the Box**

Included in Package	2m Black SuperSpeed USB 3.0 Cable Right Angle A to B - M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***

