

3 ft SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB3



StarTech.com's 3ft SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 3ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 3ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 3ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility

Applications

Features

- Cable and Connectors are compliant with USB 3.0 SuperSpeed specifications

Hardware

Warranty

Lifetime

Cable Jacket Material

PVC - Polyvinyl Chloride

Performance

| | |
|---------------|--------------------|
| Type and Rate | USB 3.0 - 5 Gbit/s |
|---------------|--------------------|

Connector(s)

| | |
|-------------|-------------------------------------|
| Connector A | USB Type-A (9 pin) USB 3.0 (5 Gbps) |
| Connector B | USB Type-B (9 pin) USB 3.0 |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Blue |
| Wire Gauge | 28 AWG |
| Cable Length | 36.0 in [91.4 cm] |
| Product Length | 36.0 in [91.4 cm] |
| Weight of Product | 1.7 oz [49 g] |

Packaging Information

| | |
|---------------------------|----------------|
| Package Length | 8.7 in [22 cm] |
| Package Width | 7.9 in [20 cm] |
| Package Height | 0.4 in [10 mm] |
| Shipping (Package) Weight | 2.0 oz [58 g] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 3 ft SuperSpeed USB 3.0 Cable A to B - M/M |
|---------------------|--|

****Product appearance and specifications are subject to change without notice.***

