

3 ft Black SuperSpeed USB 3.0 Cable A to B - M/M

Produkt ID: USB3SAB3BK



StarTech.com's 3ft Black SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 3ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 3ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 3ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifikat, rapporter och kompatibilitet

Användning

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Funktioner

- Designed and constructed to SuperSpeed USB 3.0 Specifications
 - Molded connectors with strain relief
-

Hårdvara

Garantipolicy	Lifetime
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Folieskärmad partvinnad

Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
-------------------	--------------------

Kontakt(er)

Connector A	USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9-stifts) USB 3.0

Miljö

Drifttemperatur	-10°C to 50°C (14°F to 122°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~75% RH

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	36.0 in [91.4 cm]
Produktlängd	36.0 in [91.4 cm]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	1.9 oz [53.0 g]

Förpackning

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.8 in [21.0 mm]
Fraktvikt (förpackning)	2.0 oz [58.0 g]



Vad det är i
lådan

Ingår i paketet

3ft black USB 3.0 A to B cable

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

