

3m Black SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB3MBK



The USB3SAB3MBK 3m Black USB 3.0 A-to-B cable allows you to connect your USB 3.0 type-B devices, such as your hard drive enclosures, card readers, docking stations and video capture devices, up to 3 meters away from your computer.

The USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, which helps to prevent electro-magnetic interference and ensures reliable data communication.

The 3m cable is backed by StarTech.com's Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) up to 3m away from your USB 3.0 capable desktop, laptop, or server

Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Molded connectors with strain relief
- Data transfer rates up to 5Gbps
- Offers 3m in cable length

Hardware

Warranty

Lifetime

Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Foil shielded twisted pair

Performance	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	Connector B	USB Type-B (9 pin) USB 3.0
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	28 AWG
	Cable Length	9.8 ft [3 m]
	Product Length	9.8 ft [3.0 m]
	Product Width	0.5 in [13.5 mm]
	Product Height	0.5 in [11.500 mm]
	Weight of Product	4.4 oz [125.000 g]
Packaging Information	Package Quantity	1
	Package Length	0.0 in [0.070 mm]
	Package Width	7.9 in [2.0 cm]
	Package Height	8.7 in [2.2 cm]
	Shipping (Package) Weight	4.6 oz [130.000 g]
What's in the Box	Included in Package	3m Black SuperSpeed USB 3.0 Cable A to B - M/M

**Product appearance and specifications are subject to change without notice.*

