

6 ft Black SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB6BK



StarTech.com's 6ft Black SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 6ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility

Applications

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Molded connectors with strain relief

Hardware

Warranty

Lifetime

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Foil shielded twisted pair

Performance

Type and Rate USB 3.0 - 5 Gbit/s

Connector(s)

Connector A USB Type-A (9 pin) USB 3.0 (5 Gbps)

Connector B USB Type-B (9 pin) USB 3.0

Environmental

Operating Temperature -10C to 50C (14F to 122F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0~75% RH

Physical Characteristics

Color Black

Wire Gauge 28 AWG

Cable Length 6.0 ft [1.8 m]

Product Length 6.0 ft [1.8 m]

Product Width 0.5 in [13.5 mm]

Product Height 0.5 in [11.5 mm]

Weight of Product 2.9 oz [82.2 g]

Packaging Information

Package Length 0.0 in [0.1 mm]

Package Width 4.9 in [12.5 cm]

Package Height 8.9 in [22.5 cm]

Shipping (Package) Weight 3.1 oz [87.2 g]

What's in the



Box

Included in Package 6ft black USB 3.0 A to B cablecable

****Product appearance and specifications are subject to change without notice.***

