

1 ft SuperSpeed USB 3.0 Cable A to Micro B

Product ID: USB3SAUB1



The USB3SAUB1 1-foot SuperSpeed USB 3.0 Cable (A to Micro B) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

The cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication, which ensures a quick and easy way to connect to an external storage solution for throughput of up to 5Gbps when used with a USB 3.0 host and device.

The 1ft USB 3.0 A to Micro B cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility

Applications

- Connecting Micro USB 3.0 devices to a SuperSpeed USB 3.0 compatible PC or Laptop

Features

- 1x USB 3.0 A male connector
- 1x USB 3.0 Micro-B male connector
- Shielded Twisted Pair (STP) design prevents electro-magnetic interference (EMI)
- Supports USB 3.0 data transfer rates up to 5Gbps
- Molded connectors with strain relief

- Aluminum-Mylar Foil with Braided Shielding

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	USB Type-A (9 pin, 5 Gbps)
Connector B	USB 3.0 Micro-B (10 pin, SuperSpeed)

Physical Characteristics

Color	Blue
Wire Gauge	28 AWG
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	0.8 oz [23.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.4 in [9.0 mm]
Shipping (Package) Weight	1.2 oz [33.0 g]

What's in the Box

Included in Package	1 ft SuperSpeed USB 3.0 Cable A to Micro B
---------------------	--

****Product appearance and specifications are subject to change without notice.***

