

3 ft SuperSpeed USB 3.0 (5Gbps) Cable A to Micro B

Productcode: USB3SAUB3



The USB3SAUB3 3-foot SuperSpeed USB 3.2 Gen 1 Cable (A to Micro B) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the USB 3.2 Gen 1 A to Micro B cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication to provide a quick and easy way to connect to an external storage solution with astounding throughputs of up to 5Gbps (when used with a USB 3.2 Gen 1 host and device).

The 3-foot USB 3.2 Gen 1 A to Micro B cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Connecting Micro USB 3.0 devices to a SuperSpeed USB 3.0 compatible PC or Laptop

Eigenschappen

- Shielded Twisted Pair (STP) design, helping to eliminate electro-magnetic interference (EMI)

- Data transfer rates up to 5Gbps
- Backwards compatible with USB 2.0
- Molded connectors with strain relief

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Prestaties

Type en snelheid	USB 3.0 - 5 Gbit/s
------------------	--------------------

Connector(en)

Connector A	1 - USB Type-A (9-polig) USB 3.0 (5 Gbps)
Connector B	1 - USB 3.0 Micro-B (10-polig, SuperSpeed)

Fysieke eigenschappen

Kleur	Blauw
Draaddikte	28 AWG
Kabellengte	3.0 ft [0.9 m]
Lengte product	36.0 in [91.4 cm]
Breedte product	0.0 in [0.0 mm]
Hoogte product	0.0 in [0.0 mm]
Gewicht product	1.5 oz [43.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	6.9 in [17.6 cm]
Package Width	7.8 in [19.9 cm]

Package Height 0.7 in [1.7 cm]

Verzendgewicht
(verpakt) 1.8 oz [52.0 g]

Wat wordt er
meegeleverd

Meegeleverd 1 - 3 ft SuperSpeed USB 3.0 Cable A to Micro B

Garantiebepalinge
n

Warranty Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.