

3 ft SuperSpeed USB 3.0 Cable A to Micro B

Product ID: USB3SAUB3



The USB3SAUB3 3-foot SuperSpeed USB 3.0 Cable (A to Micro B) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the USB 3.0 A to Micro B cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication to provide a quick and easy way to connect to an external storage solution with astounding throughputs of up to 5Gbps (when used with a USB 3.0 host and device).

The 3-foot USB 3.0 A to Micro B cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility

Applications

- Connecting Micro USB 3.0 devices to a SuperSpeed USB 3.0 compatible PC or Laptop

Features

- Backwards compatible with USB 2.0
- Data transfer rates up to 5Gbps
- Molded connectors with strain relief
- Shielded Twisted Pair (STP) design, helping to eliminate electro-magnetic interference (EMI)

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB 3.0 Micro-B (10 pin, SuperSpeed)

Physical Characteristics

Color	Blue
Wire Gauge	28 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Weight of Product	1.5 oz [43 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.4 in [9 mm]
Shipping (Package) Weight	1.8 oz [52 g]

What's in the Box

Included in Package	3 ft SuperSpeed USB 3.0 Cable A to Micro B
---------------------	--------------------------------------------

**Product appearance and specifications are subject to change without notice.*

