

Dual-Monitor USB 3.0 Docking Station with HDMI & DVI/VGA

Product ID: USB3SDOCKHDV

This USB 3.0 dock combines three USB 3.0 ports, headphone and microphone audio connectors, and a Gigabit Ethernet RJ45 port, into a single docking station for maximum productivity.

Offering flexible dual video combinations right out-of-the-box, this universal laptop docking station features HDMI, DVI and VGA external monitor outputs. Each video output supports HD video resolutions (2048x1152 max) and HD video playback for an ideal solution to expanding your notebook's video capability.

Available display combinations:

- HDMI + VGA
- HDMI + DVI

The built-in USB hub features three USB 3.0 ports for connecting extra peripherals such as external hard drives or a wired mouse, as if they are connected directly to your laptop.

The integrated RJ45 Ethernet port supports speeds of 10/100/1000 Mbps, giving you an instant connection to a wired network.

StarTech.com laptop docking stations can be used for cost savings and faster deployment with just a single cable. This USB 3.0 Docking Station is backed by a competitive 3-year warranty and free lifetime Technical Support.

Certifications, Reports and Compatibility

Applications

- Hot/Remote desks
- Convert laptop to desktop workstation
- Shared workspaces

Features

- Connect to wired networks with the built-in 10/100/1000 Mbps compatible RJ45 Ethernet port
- TAA compliant GSA schedule purchases
- Connect devices with 3 USB 3.0 ports
- Connect dual monitors using either HDMI + DVI-D, or HDMI + VGA combinations

Hardware

Warranty

3 Years

4K Support	No
Fast-Charge Port(s)	No
Displays Supported	2
Bus Type	USB 3.0
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, USB 3.0
Chipset ID	DisplayLink - DL-3900 Genesys Logic - GL3520 Realtek - RTL8211E

Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Analog Resolutions	2048x1152 (VGA)
Maximum Digital Resolutions	1920x1200 (DVI-D) 1920x1080 (HDMI) Lower resolutions are also supported.
Audio Specifications	The HDMI port supports audio output
Type and Rate	USB 3.0 - 5 Gbit/s
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	DVI-D (25 pin) 3.5 mm Mini-Jack (3 Position) USB Type-A (9 pin) USB 3.0 (5 Gbps) USB Type-B (9 pin) USB 3.0 HDMI (19 pin)
-------------------	---



VGA (15 pin, High Density D-Sub)

RJ-45

Software

OS Compatibility	Windows XP SP3 (32-bit), Vista, 7, 8, 8.1, 10 macOS 10.6 - 10.12, 10.14 - 10.15, 11.0
------------------	--

Special Notes / Requirements

System and Cable Requirements	USB 3.0 enabled computer system with available USB 3.0 port HDMI (and either DVI-D or VGA if dual display is desired) enabled display device(s) e.g. monitor, projector, HTDVI, etc. with cables Available AC electrical outlet
-------------------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.9 A
Output Voltage	5 DC
Output Current	4 A
Center Tip Polarity	Positive
Plug Type	B
Power Consumption (In Watts)	20

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0~90% RH

Physical Characteristics

Color	Black
Material	Plastic



Cable Length	35.4 in [90 cm]
Product Length	12.0 in [30.4 cm]
Product Width	7.0 in [17.8 cm]
Product Height	1.7 in [44 mm]
Weight of Product	10.4 oz [295 g]

Packaging Information

Package Length	11.7 in [29.6 cm]
Package Width	7.7 in [19.5 cm]
Package Height	2.6 in [66 mm]
Shipping (Package) Weight	31.0 oz [878 g]

What's in the Box

Included in Package	0.9m USB 3.0 Cable
	Docking Station
	Universal Power Adapter (NA/EU/UK/AU)
	Installation CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

