

6 ft Black SuperSpeed USB 3.0 Extension Cable A to A - M/F

Produkt ID: USB3SEXT6BK



The USB3SEXT6BK SuperSpeed USB 3.0 extension cord (A-A), offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, this USB 3.0 male to female cable extends a USB 3.0 cable connection by 6-feet, and delivers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our USB 3.0 extension cables features high quality Shielded Twisted Pair (STP) construction, helping to prevent electromagnetic interference and ensuring reliable data communication.

The USB3SEXT6BK is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifikat, rapporter och kompatibilitet

Användning

- Extend your USB 3.0 Super Speed cable by up to 6ft

Funktioner

- 1x USB 'A' Male Connector
- Data transfer rates up to 5Gbps
- 1x USB 'A' Female Connector

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- High quality Shielded Twisted Pair (STP) construction
- Backward compatible with USB 2.0

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Folieskärmad partvinnad

Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
-------------------	--------------------

Kontakt(er)

Connector A	USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	USB Type-A (9-stifts) USB 3.0 (5 Gbps)

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	6.0 ft [1.8 m]
Produktlängd	6.0 ft [1.8 m]
Produktbredd	0.7 in [18.0 mm]
Produkthöjd	0.4 in [11.0 mm]
Produktvikt	2.7 oz [76.0 g]

Förpackning

Förpackningsantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]



Package Height 0.7 in [17.0 mm]

Fraktvikt
(förpackning) 3.0 oz [86.0 g]

Vad det är i
lådan

Ingår i paketet 6 ft Black SuperSpeed USB 3.0 Extension Cable A to A - M/F

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

