

6 ft SuperSpeed USB 3.0 Extension Cable A to A - M/F

Product ID: USB3SEXTAA6



The USB3SEXTAA6 SuperSpeed USB 3.0 extension cable (1.8m, A-A), offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, this USB 3.0 male to female cable extends a USB 3.0 cable connection by up to 1.8 meters and delivers the full USB 3.0 bandwidth of 5Gbps, supporting maximum throughput between compatible devices when used with a USB 3.0 host and device.

Our USB 3.0 extension cord features high quality Shielded Twisted Pair (STP) construction, helping to prevent electromagnetic interference and ensuring reliable data communication.

The USB3SEXTAA6 is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility

Applications

- Extend your USB 3.0 Super Speed cable by 6ft

Features

- 1x USB 'A' Male Connector
- 1x USB 'A' Female Connector
- Designed and constructed to SuperSpeed USB 3.0 Specifications
- High quality Shielded Twisted Pair (STP) construction

- Data transfer rates up to 5Gbps
- Backward compatible with USB 2.0

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Foil shielded twisted pair

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Physical Characteristics

Color	Blue
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.5 in [13.5 mm]
Product Height	0.5 in [11.5 mm]
Weight of Product	2.9 oz [83.2 g]

Packaging Information

Package Length	0.0 in [0.1 mm]
Package Width	4.9 in [12.5 cm]
Package Height	8.9 in [22.5 cm]
Shipping (Package) Weight	3.1 oz [88.2 g]



**What's in the
Box**

Included in Package	6ft SuperSpeed USB 3.0 Extension Cable A to A - M/F
---------------------	---

****Product appearance and specifications are subject to change without notice.***

