

External V.92 56K USB Fax Modem

Product ID: USB56KEM2



The USB56KEM2 external 56K USB modem (V.92/V.90) converts a standard USB port into an external 56K dial-up modem. This provides an ideal solution for applications that require a cost-effective way to connect to the Internet through dial-up, or simple fax modem capabilities.

This lightweight device provides portable convenience and is powered through the USB bus, eliminating the need for an external power adapter and saving the hassle of having to find a wall outlet.

With support for transfer rates up to 56 Kbps (data) and 14.4 Kbps (fax), this convenient USB modem is the ideal solution for a dial-up Internet connection or PC fax machine.

The USB56KEM2 external 56k USB modem offers broad operating system compatibility (including Windows 7 32-bit and 64bit), backed by our 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Add dial-up support to a desktop, laptop, or netbook when broadband access is not available.
- Turn a PC into a fax machine, capable of sending and receiving faxes.

Features

- Data transfer rates up to 56Kbps (down) and 48Kbps (up)
- Compatible with V.92, V.90, and V.34 data modes

- Compatible with T.31, V.17, V.29, V.27, and V.21 Fax modes
- Telephone Answering Machine (TAM) support
- Auto fallback adjusts the connection speed, based on connection quality
- Hot-swap and Plug-and-Play compatible
- Powered directly from the USB port
- USB revision 1.1/2.0 compliant
- WHQL certified drivers

Hardware

Warranty	2 Years
Ports	1
Bus Type	USB 2.0
Industry Standards	Modem Modulation ITU-T V.92, V.90, K56flex, V.34, V.32, v.23, V.22 bis, V.22, V.21, Bell 212A and 103 Fax Modulation V.17, V.29, V.27 Ter, V.21 channel 2 Data Compression - V.44
Chipset ID	LSI - SV92U2C

Performance

Maximum Data Transfer Rate	56 Kbps Down 48 Kbps Up 14.4 Kbps Fax
----------------------------	---

Connector(s)

External Ports	RJ-11 USB Type-A (4 pin) USB 2.0
----------------	---

Software



OS Compatibility	Windows 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000, ME Windows Server 2008 R2
------------------	--

Microsoft WHQL Certified	Yes
--------------------------	-----

Indicators

LED Indicators	Red - Power
----------------	-------------

Power

Power Consumption (In Watts)	0.1W
------------------------------	------

Environmental

Operating Temperature	0C to 70C (32C to 158C)
Storage Temperature	-20C to 85C (-4C to 185C)
Humidity	5~95% RH

Physical Characteristics

Color	Black
Product Length	7.7 in [19.5 cm]
Product Width	1.3 in [32 mm]
Product Height	0.8 in [21 mm]
Weight of Product	1.8 oz [50 g]

Packaging Information

Package Length	5.5 in [14 cm]
Package Width	1.5 in [37.5 mm]
Package Height	5.2 in [13.1 cm]
Shipping (Package) Weight	2.1 oz [60 g]

What's in the Box

Included in Package	USB Modem 6ft RJ-11 Phone/Modem cable
---------------------	--



Driver CD

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

