

External 56K USB Modem

Product ID: USB56KEM



This external 56k USB modem converts a USB port into an external 56k dialup modem, providing the ideal solution for applications that require fax modem capability, or simply a cost-effective way to connect to the Internet through dialup.

This lightweight device provides portable convenience, and is powered through the USB bus - eliminating the need for an external power adapter and saving the hassle of having to find a wall outlet.

With support for PCM Upstream, quick connect and v.44 data and error correction, this external USB modem provides the versatility and convenience needed to get true value from a dialup connection.

Certifications, Reports and Compatibility

Applications

Features

- V .92 modem supports data receive rates up to 56Kbps and send rates up to 48kbps
- Supports PCM upstream and quick connect
- Ideal for dial-up internet services with V.44 data compression
- Also supports fax send/receive rates up to 14.4Kbps

Performance

Warranty	2 Years
General Specifications	Data Receive Rate: 56Kbps
	Data Send Rate: 48Kbps
	Modem Modulation: ITU-T V.92, V.90, K56flex, V.34, V.32, v.23, V.22 bis, V.22, V.21, Bell 212A and 103
	PCM Upstream: Yes
	Quick Connect: Yes
	Data Compression: V.44 for dial-up internet
	Fax Transfer Rates: 14.4Kbps Send/Receive
	Fax Modulation: V.17, V.29, V.27 Ter, V.21 channel 2
	TAPI Compliant: Yes

Connector(s)

Connector Type(s)	RJ-11
	USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2
------------------	--

Physical Characteristics

Color	Black
-------	-------

Packaging Information

Package Length	5.0 in [12.7 cm]
Package Width	1.3 in [33 mm]
Package Height	7.7 in [19.5 cm]
Shipping (Package) Weight	3.5 oz [100 g]

What's in the Box

Included in Package	USB Modem
	Driver CD



User Guide

****Product appearance and specifications are subject to change without notice.***

