

1m USB 2.0 A to Left Angle B Cable - M/M

Produkt ID: USBAB1ML



The USBAB1ML 1-meter USB printer cable features one USB-A male connector and one left-angle USB-B male connector, providing a high-quality connection to USB 2.0 peripherals and enabling installation in narrow spaces.

Constructed of only top quality materials and expertly designed for durability, this angled USB cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a 1m USB 2.0 A to Right Angle B Cable (USBAB1MR), which provides the same convenience as this left-angled cable, but allows you to connect to your USB device from the opposite direction.

Certifikat, rapporter och kompatibilitet



Användning

- Connecting USB 2.0 devices such as printers, scanners or external USB hard drives, even in hard-to-reach areas and narrow spaces

Funktioner

- 1x USB-A male connector

- 1x Left-angled USB-B male connector
- Aluminum-Mylar Foil with Braided Shielding
- Supports USB 2.0 data transfer rates up to 480 Mbps

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Connector B	1 - USB B (4-stifts)

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-10°C to 30°C (14°F to 86°F)
Luftfuktighet	30%-75% RH

Utseende

Färg	Svart
Kontakttyp	Rak till vänstervinklad
Tråddimension	24/28 AWG
Kabellängd	3.3 ft [1 m]
Produktlängd	3.3 ft [1.0 m]
Produktbredd	0.5 in [1.2 cm]
Produkthöjd	0.3 in [0.8 cm]
Produktvikt	1.3 oz [35.6 g]

Förpackning

Förpackningsantal	1
Paketets längd	5.4 in [13.7 cm]
Paketets bredd	5.0 in [12.7 cm]
Paketets höjd	0.7 in [1.7 cm]
Fraktvikt (förpackning)	1.6 oz [46.0 g]

Vad det är i lådan

Ingår i paketet	1 - 1m USB 2.0 A to Left Angle B Cable - M/M
-----------------	--

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.