

## 1m USB 2.0 A to Right Angle B Cable - M/M

Produkt ID: USBAB1MR



The USBAB1MR 1-meter USB printer cable features one USB 'A' male connector and one right-angle USB 'B' male connector, providing a high-quality connection to USB 2.0 peripherals.

The right-angled USB 'B' connector allows you to connect to your hard-to-reach USB 2.0 printers, scanners, external hard drives, etc. and enables installation in narrow spaces.

Constructed of only top quality materials and expertly designed for durability, this angled USB cable is backed by StarTech.com's Lifetime Warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Connecting USB 2.0 devices such as printers, scanners or external USB hard drives, even in hard to reach areas and narrow spaces

### Funktioner

- 1x USB 'A' male connector
- 1x Right-angled USB 'B' male connector
- Aluminum-Mylar Foil with Braided Shielding
- Supports USB 2.0 data transfer rates up to 480 Mbps

---

#### Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

---

#### Kontakt(er)

Connector A	USB Type-A (4-stifts) USB 2.0
Connector B	USB B (4-stifts)

---

#### Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-10°C to 30°C (14°F to 86°F)
Luftfuktighet	30%-75% RH

---

#### Utseende

Färg	Svart
Kontakttyp	Rak till högervinklad
Tråddimension	24/28 AWG
Kabellängd	39.4 in [100 cm]
Produktlängd	39.4 in [100.0 cm]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	1.3 oz [35.5 g]

---

#### Förpackning

Förpackningsantal	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]



Package Height 0.0 in [0.1 mm]

Fraktvikt  
(förpackning) 1.4 oz [41.0 g]

---

Vad det är i  
lådan

Ingår i paketet 1m USB 2.0 A to Right Angle B Cable - M/M

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

