

2m USB 2.0 A to Right Angle B Cable - M/M

Product ID: USBAB2MR



The USBAB2MR 2-meter USB printer cable features one USB 'A' male connector and one right-angle USB 'B' male connector, providing a high-quality connection to USB 2.0 peripherals.

The right-angled USB 'B' connector allows you to connect to your hard-to-reach USB 2.0 printers, scanners, external hard drives, etc. and enables installation in narrow spaces.

Constructed of only top quality materials and expertly designed for durability, this angled USB cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a 2m USB 2.0 A to Left Angle B Cable (USBAB2ML), which provides the same convenience as this right-angled cable, but allows you to connect to your USB device from the opposite direction.

Certifications, Reports and Compatibility

Applications

- Connecting USB 2.0 devices such as printers, scanners or external USB hard drives, even in hard to reach areas and narrow spaces

Features

- 1x USB 'A' male connector
- 1x Right-angled USB 'B' male connector
- Aluminum-Mylar Foil with Braided Shielding

- Supports USB 2.0 data transfer rates up to 480 Mbps

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB B (4 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	24/28 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.6 in [15.4 mm]
Product Height	0.4 in [10.0 mm]
Weight of Product	2.1 oz [60.6 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]



Package Height 0.0 in [0.1 mm]

Shipping (Package) Weight 2.3 oz [66.1 g]

What's in the Box

Included in Package 2m USB 2.0 A to Right Angle B Cable - M/M

****Product appearance and specifications are subject to change without notice.***

