

Micro-USB Charge-and-Sync Cable M/M - Right-Angle Micro-USB - 30/24 AWG - 1 m (3 ft.)

Product ID: USBAUB1MRA



This 30/24 Micro-USB cable features 24 AWG wire to provide the full power you need to charge your mobile devices faster.

Plus, the right-angled Micro-USB connector is great for charging your mobile devices in a car, or for accessing your mobile device while it's connected to a wall charger or computer.

Different phones and tablets require specific amounts of power to charge efficiently. While a phone may only require 1.0A of power, a tablet may need 2.4A.

This 30/24 cable is designed to deliver full power to your mobile devices so that all of your devices can charge at the expected speed.

The right-angled Micro-USB connector lets you connect to ports that are difficult to reach, which is perfect for charging your car-mounted mobile devices. Even while you're charging your mobile device, you can use it to text, work or game, without the cable getting in the way.

The angled connector also prevents the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection point, preventing unnecessary stress and damage to the cable and device port.

Replace the Micro-USB cable that came with your mobile device, or keep one as a spare while traveling so that your mobile devices will be ready to use while you're on the road.

The USBAUB1MRA 1-meter cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Micro-USB mobile devices
- Replace the cable that came with your Micro-USB device or keep one as a spare while traveling

Features

- Provide full charging power to your Micro-USB mobile devices
- Connect to your device even in hard to reach areas and tight spaces
- Guaranteed reliability with our lifetime warranty

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB Micro-B (5 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
-------	-------

Connector Style	Straight to Right Angle
Wire Gauge	24/30 AWG
Cable Length	39.4 in [1000 mm]
Product Length	36.0 in [91.4 cm]
Product Width	0.0 in [0.1 cm]
Product Height	0.1 in [0.2 cm]
Weight of Product	1.0 oz [27.0 g]

Packaging Information

Package Quantity	1
Package Length	5.3 in [13.5 cm]
Package Width	5.1 in [13.0 cm]
Package Height	0.5 in [1.3 cm]
Shipping (Package) Weight	1.1 oz [30.0 g]

What's in the Box

Included in Package	1 - 1m Right-Angle Micro-USB 2.0 Charging Cable for Tablets and Phones
---------------------	--

****Product appearance and specifications are subject to change without notice.***