

Micro-USB Charge-and-Sync Cable M/M - Right-Angle Micro-USB - 24 AWG - 0.5 m

Product ID: USBAUB50CMRA



This Micro-USB cable features 24 AWG wire to provide the full power you need to charge your mobile devices faster. The cable features a right-angled Micro-USB connector, so it's great for charging your mobile devices in a car, or for accessing your mobile device while it's connected to a car charger or computer.

Different phones and tablets require specific amounts of power to charge efficiently. While a phone may only require 1.0A of power, a tablet may need 2.4A.

This Micro-USB cable is designed to deliver full power to your mobile devices so that all of your devices can charge at the expected speed .

The right-angled Micro-USB connector lets you connect to ports that are difficult to reach, which is perfect for charging your car-mounted mobile devices. Even while you're charging your mobile device, you can use it to text, work or game, without the cable getting in the way.

The angled connector also prevents the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection point, preventing unnecessary stress and damage to the cable and device port.

Replace the Micro-USB cable that came with your mobile device, or keep one as a spare while you're traveling so that your mobile devices are ready to use while you're on the road. The short 0.5 m/1.5 ft. cable length makes this an excellent solution for close-range connections and portable applications such as charging with a mobile charging bank, public charging stations or your laptop.

The USBAUB50CMRA 0.5-meter cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Micro-USB mobile devices
- Replace the cable that came with your Micro-USB device or keep one as a spare while traveling

Features

- Provide full charging power to your Micro-USB mobile devices
- Connect to your device even in hard to reach areas and tight spaces
- Portable design fits nicely into any carrying case

Hardware	Warranty	1 Year
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB Micro-B (5 pin)
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics	Color	Black
	Connector Style	Straight to Right Angle
	Wire Gauge	24/30 AWG
	Cable Length	19.7 in [5 cm]
	Product Length	19.7 in [5.0 cm]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	0.6 oz [18.000 g]
Packaging Information	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.2 in [5.000 mm]

Shipping (Package) Weight	0.8 oz [24.000 g]
------------------------------	-------------------

What's in the Box	Included in Package	Micro-USB Cable
------------------------------	---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***

