

Standalone 1:5 USB Flash Drive Duplicator and Eraser – Flash Drive Copier

Product ID: USBDUP15



The USBDUP15 OnetoFive USB flash drive duplicator and eraser lets you quickly clone up to five backups of a single USB flash drive, or securely erase up to five flash drives, without connecting to a host computer.

Featuring a compact lightweight design that you can carry anywhere, and standalone operation that does not require a host computer, the flash drive duplicator and eraser has a small desktop footprint and is great for travel. Perfect for software and marketing content distribution in the office or on-the-go.

With an easy-to-read LCD display and intuitive four button menu operation, the USBDUP15 ensures hassle-free setup and control. The menu gives you push-button access to many value-added features that ensure simple task management such as: Capacity & Speed Check, Copy & Compare, Asynchronous Copy, and many more. It also provides numerous advanced setup options for experienced users.

This versatile device is both hard drive cloner and eraser in one, and offers two duplication modes (File & System Copy / Whole Copy) with up to 1.5GB/m at Whole Copy mode. It offers three erase modes (Quick Erase / Full Erase / DoD Erase) giving you the freedom to choose the best solution for your application.

The USBDUP15 is TAA compliant and backed by a 2-year StarTech.com warranty and lifetime technical support.

Note: The USBDUP15 flash drive duplicator supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a hard drive docking station or USB enclosure (sold separately)

Certifications, Reports and Compatibility

Applications

- Quickly backup USB flash drives without a host computer
- Create exact copies of a USB flash drive in law enforcement and forensic investigations

- Thoroughly erase data from a flash drive, for added data security and peace of mind
- Software and operating system updating and distributions
- Marketing collateral copying and distribution
- Rich media coping and distributions
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives

Features


- High-speed duplication at up to 1.5GB per minute
- Erase up to 5 USB flash drives with single-pass and multi-pass overwriting/DoD erasing
- 1:5 standalone duplication with 2 duplication modes
- Supports USB 3.0/2.0/1.1 flash drives
- Compact, lightweight design
- TAA compliant
- Built-in LCD display
- Check drive capacity, quality and speed with intuitive task management
- Supports both Asynchronous and Synchronous copy modes, for quick batch swapping with 64 MB of internal memory

Hardware

Warranty	2 Years
Bus Type	USB 2.0
Number of Drives	6
Compatible Drive Types	USB Flash Drive
Drive Installation	Removable
Buffer Size	64 MB

Performance

Duplication Modes	System and File
-------------------	-----------------



Sector by Sector (Whole Drive)

Duplication Speed	1.5GBpm
Erase Modes	Quick Erase
	1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)
	3-Pass Overwrite
MTBF	176,549 hours

Connector(s)

Drive Connectors	USB Type-A (4 pin) USB 2.0
------------------	----------------------------

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

System and Cable Requirements	For duplication, the destination drives must be of equal or greater capacity than the source drive.
	Supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure (sold separately)

Indicators

LED Indicators	Green (Activity/Successful Copy)
	Red (Error)

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	5 DC
Output Current	2
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10



Environmental

Operating Temperature	5C ~ 45C (41F ~ 113F)
Storage Temperature	-20C ~ 85C (-4F ~ 185F)
Humidity	5% ~ 95% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	6.6 in [16.7 cm]
Product Width	4.7 in [12 cm]
Product Height	1.0 in [25 mm]
Weight of Product	11.2 oz [318 g]

Packaging Information

Package Length	9.1 in [23.1 cm]
Package Width	7.1 in [18 cm]
Package Height	3.2 in [82 mm]
Shipping (Package) Weight	26.2 oz [742 g]

What's in the Box

Included in Package	Duplicator
	Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

