

6 ft Black USB 2.0 Extension Cable A to A - M/F

Product ID: USBEXTAA6BK



The USBEXTAA6BK 6-foot USB Extension Cable (A-A) features 1 USB A male connector and 1 USB A female connector, extending the connection between USB 2.0 devices by up to 6 feet - an ideal solution for better placement of peripheral devices, or adding flexibility to existing USB ports.

This high quality USB extension cable is fully rated for use with USB 1.1 and USB 2.0 devices, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend your USB connection to connect a USB printer or any USB peripheral device to a PC or Mac at high-performance data transfer speed

Features

- Supports data transfer rates up to 480 Mbps
- Designed and constructed to USB 2.0 specifications
- Molded strain relief

Hardware	Warranty	1 Year
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride

	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB Type-A (4 pin) USB 2.0
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics	Color	Black
	Wire Gauge	24/28 AWG
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]
	Product Width	0.6 in [15.000 mm]
	Product Height	0.6 in [14.000 mm]
	Weight of Product	2.3 oz [65.000 g]
Packaging Information	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.9 in [22.000 mm]
	Shipping (Package) Weight	2.5 oz [70.000 g]
What's in the Box	Included in Package	6 ft Black USB 2.0 Extension Cable A to A - M/F

****Product appearance and specifications are subject to change without notice.***

