

3m White USB 2.0 Extension Cable A to A - M/F

Product ID: USBEXTPAA3MW



The USBEXTPAA3MW 3m White USB 2.0 Extension Cable features a USB 'A' male connector and a USB 'A' female connector, enabling you to extend the connection distance between your USB 2.0 devices by up to 1-meter – allowing for better placement of your peripheral devices, or adding flexibility to your existing USB ports.

The cable features thin USB connector moldings which allow you to simplify your connections, and plug into tight fitting locations.

Designed and constructed for maximum durability, this high quality USB 2.0 extension cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Extend the length of your USB 2.0 A to B cable by up to 3m – for convenient placing of your USB 2.0 peripherals

Features

- 1x USB 'A' male connector
- All white construction
- Thin USB 2.0 connector moldings, with strain relief
- Supports high-speed data transfer rates of up to 480 Mbps
- 1x USB 'A' female connector

Hardware	Warranty	1 Year
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride

	Cable Shield Material	Aluminum-Mylar Foil with Drain
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB Type-A (4 pin) USB 2.0
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics	Color	White
	Connector Style	Straight
	Wire Gauge	24/28 AWG
	Cable Length	9.8 ft [3 m]
	Product Length	9.8 ft [3.0 m]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	1.7 oz [47.800 g]
Packaging Information	Package Quantity	1
	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.0 in [0.070 mm]
	Shipping (Package) Weight	1.9 oz [53.300 g]
What's in the Box	Included in Package	3m White USB Extension Cable - A to A M/F

**Product appearance and specifications are subject to change without notice.*

