

10 ft Beige A to B USB 2.0 Cable - M/M

Produkt-ID: USBFAB_10



The USBFAB_10 10ft USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

Merkmale

- Unterstützt USB-Datenübertragungsraten bis zu 480 MBit/s

Hardware

Garantiebestimmungen Lifetime

Steckverbinderplatten Nickel

Leistung

Max. Kabellänge 16.4 ft [5 m]

Typ und Rate USB 2.0 - 480 Mbit/s

Steckverbinder

Steckverbinder A 1 - USB 2.0 Typ-A (4 pin, 480Mbit/s)

Steckverbinder B 1 - USB B (4-polig)

Physische Eigenschaften

Farbe Beige

Kabellänge 10.0 ft [3.0 m]

Produktlänge 10.0 ft [3.0 m]

Produktgewicht 3.3 oz [93 g]

Verpackungsinformationen

Paketmenge 1

Paketlänge 6.5 in [16.6 cm]

Paketbreite 5.0 in [12.6 cm]

Pakethöhe 0.7 in [1.8 cm]

Versandgewicht (Verpackung) 3.4 oz [96.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - 10 ft Beige A to B USB 2.0 Cable - M/M

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.