

3 ft Panel Mount USB Cable B to B - F/M

Product ID: USBPNLBFBM3



The USBPNLBFBM3 3ft Panel Mount USB Cable features one USB-B male connector on one end and a USB-B panel mount female port on the other, providing a convenient solution for custom enclosures (e.g. internally mounted hard drives).

Offering 3ft in cable length, the adapter allows you to extend the connection as needed within the system case.

The USBPNLBFBM3 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Add a USB-B female port to your custom enclosures

Features

- Offers 3' in cable length
- 1x USB-B male connector
- 1x USB-B panel mount female port

Hardware	Warranty	1 Year
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride

	Cable Shield Material	Aluminum-Mylar Foil with Braid
Connector(s)	Connector A	USB B (4 pin)
	Connector B	USB B (4 pin)
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	24/28 AWG
	Cable Length	36.0 in [9.1 cm]
	Product Length	36.0 in [9.1 cm]
	Product Width	1.5 in [39.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	1.6 oz [45.000 g]
Packaging Information	Package Quantity	1
	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.0 in [0.070 mm]
	Shipping (Package) Weight	1.8 oz [50.500 g]
What's in the Box	Included in Package	3 ft Panel Mount USB Cable B to B - F/M

**Product appearance and specifications are subject to change without notice.*

