

Secure Charging USB Data Blocker Adapter – Male to Female USB-A Charge-Only Adapter – No-Data Charge/Power-Only Adapter for Phone/Tablet – Data Blocking USB Protector Adapter

Product ID: USBSCHAAMF



This USB-A male to USB-A female Data Blocker adapter lets you securely charge your device by establishing a power-only connection between your device and the host system or power source. Equipped with no-data USB-A male connector with a unique cut-away design, this secure adapter prevents malware attacks and data thefts, and provides a safe way to charge your mobile devices.

Power-Only USB-A to A Adapter

The USB-A male port of this adapter does not have physical data pins, resulting in an adapter with physical barrier for data transmission. This adapter allows you to charge your mobile devices from a laptop or desktop computer while eliminating any possibility of

- Data theft from the host computer
- Data corruption on the host computer
- Infection from spyware/malware or viruses being transmitted from the mobile device to the host network

Handy Adapter for Everyday Use

Portable 1.3"L x 0.7"W x 0.4"H adapter fits into your pocket or laptop bag, and lets you safely charge your smart phones, tablets, headphones, cameras, etc. in public charging stations/ports in airports, hotels and restaurants. Absence of data lines also makes this adapter safe to use in government, defense, corporate and educational environments, where connecting your mobile device may be prohibited.

Smart, Powerful and Versatile Cable

High throughput adapter delivers 5V up to 2.4A (12W max.). Smart on-board chip identifies the device's power requirements and adjusts the output accordingly. Use your existing USB-A to C, Lightning, micro-B cables to charge your appropriate devices from all USB-A power outlets - from host computers to wall chargers.



Robust and Reliable Construction

The adapter's mold is made from tough TPE plastic that offers high resilience to fraying and scratches, making it ideal for everyday rough use. Aluminium-Mylar foil shielding provides noise-free DC power to your device.

Comprehensive Product Testing & Expert Technical Support

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

USBSCHAAMF is backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility







Applications

Features

- USB-A DATA BLOCKER ADAPTER: Charge-Only design without data pins provides physical data blocking, prevents data theft/corruption and leak prevention while stopping spyware/malware attacks on smartphones, tablets & battery powered mobile devices
- SECURE CHARGING ADAPTER: Tiny pocket sized adapter is easy to carry, charge devices anywhere using your data blocking charger cable adapter, Ideal for high-security use in public, corporate, defence & educational environments
- VERSATILE ADAPTER: The USB Data Protector delivers 5V at 2.4A (12W max) & works with all USB-A cables and hosts so you can use your existing USB-A to C/Lightning/Micro-USB cable to charge your devices
- ROBUST CONSTRUCTION: Durable and Rugged enclosure built for portability and on the go use with public charging ports in airports, shopping malls & hotels, Recommended cables: RUSBLTMM1MB(Lightning), RUSB2AC1MB(USB-C)
- SPECS: Dimensions: 1.3"L x 0.7"W x 0.4"H USB-A female to male adapter Throughput: 5V, 2.4A (12W max) Rugged TPE Shell Unique cut-away design shows secure power-only lines Backed by StarTech.com for lifetime

Hardware			
	Warranty	Lifetime	

Active or Passive Adapter Passive



Connector Plating	Nickel
-------------------	--------

Cable Jacket Material TPE - Thermoplastic Elastomers

Performance

Type and Rate USB 2.0 - 480 Mbit/s

Connector(s)

Connector A 1 - USB 2.0 Type-A (4 pin, 480Mbps)

1 - USB 2.0 Type-A (4 pin, 480Mbps)

Special Notes / Requirements

System and Cable Requirements

Unique cut-away design shows secure power-only lines

Power

Output Voltage 5V DC

Output Current 2.4A

Power Consumption (In

Watts)

12W

Environmental

Operating Temperature -20C to 60C (4F to 140F)

Storage Temperature

20C to 28C (68F to 82F)

Humidity

10%-80% RH

Physical Characteristics

Color Black

Product Length 1.8 in [4.5 cm]

Product Width 0.6 in [1.5 cm]

Product Height 0.4 in [1.0 cm]

Weight of Product 0.3 oz [9.0 g]

Packaging Information

Package Quantity



Package Length 5.0 in [12.8 cm]

Package Width 3.5 in [9.0 cm]

Package Height 0.4 in [1.0 cm]

Shipping (Package) 0.4 oz [11.0 g]

Weight

What's in the Box

Included in Package 1 - USB Adapter

^{*}Product appearance and specifications are subject to change without notice.