

10 ft Micro USB Cable - A to Micro B

Produkt-ID: UUSBHAUB10



The UUSBHAUB10 10-foot USB A to Micro USB cable features one USB 'A' male connector, and one 'Micro-B' male connector, providing a high quality connection to USB 2.0 mobile devices (such as BlackBerry® or Android-based cellular phones, digital cameras, PDA's, Tablet PC devices and GPS systems) that use a Micro USB connector to a USB capable computer for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Zertifikate Berichte und Kompatibilität



Anwendungen

- An ideal replacement cable for connecting mobile devices to a USB capable computer

Merkmale

- Supports high speed data transfer rates up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding

- High quality USB 'A' and USB 'Micro-B' connectors
- Durable PVC construction

Hardware

Garantiebestimmungen	Lifetime
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

Typ und Rate	USB 2.0 - 480 Mbit/s
--------------	----------------------

Steckverbinder

Steckverbinder A	1 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
Steckverbinder B	1 - USB Micro-B (5-polig)

Umgebungsbedingungen

Betriebstemperatur	-20°C to 60°C (-4°F to 140°F)
Lagertemperatur	-10°C to 30°C (14°F to 86°F)
Feuchtigkeit	30%-75% RH

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	24/30 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	0.6 in [1.6 cm]
Produkthöhe	0.3 in [0.7 cm]
Produktgewicht	2.4 oz [68.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	5.8 in [14.8 cm]
Paketbreite	5.0 in [12.6 cm]
Pakethöhe	0.7 in [1.9 cm]
Versandgewicht (Verpackung)	2.8 oz [78.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10 ft Micro USB Cable - A to Micro B
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.