

1m Micro USB Cable - A to Micro B

Product ID: UUSBHAUB1M



The UUSBHAUB1M 1-meter USB-A to Micro USB cable features one USB 'A' male connector, and one 'Micro-B' male connector, providing a high quality connection between USB 2.0 mobile devices that use a Micro USB connector (such as BlackBerry or Android-based smart phones, digital cameras, PDAs, Tablet PC devices and GPS systems) and a USB-capable computer for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certifications, Reports and Compatibility



Applications

- An ideal replacement cable for connecting mobile devices that use a Micro USB connector to a computer through a standard USB (type A) port

Features

- Supports high speed USB data transfer rates up to 480 Mbps
- Durable PVC construction
- Aluminum-Mylar Foil with Braided Shielding
- High quality USB 'A' and USB 'Micro-B' connectors

Hardware	Warranty	1 Year
	Connector Plating	Nickel

	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB Micro-B (5 pin)
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	39.4 in [10 cm]
	Product Length	39.4 in [10.0 cm]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	1.1 oz [32.000 g]
Packaging Information	Package Quantity	1
	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.0 in [0.070 mm]
	Shipping (Package) Weight	1.3 oz [38.000 g]
What's in the Box	Included in Package	1m Micro USB Cable - A to Micro B

**Product appearance and specifications are subject to change without notice.*

