

Component / VGA Video and Audio to HDMI Converter - PC to HDMI - 1920x1200

Produkt ID: VGA2HD2



The VGA2HD2 Component/VGA to HDMI® Video Converter offers seamless conversion from an analog VGA or Component video source, such as a Computer, DVR, or DVD player, to a digital HDMI® output.

The converter helps reduce equipment costs by eliminating the need to upgrade individual analog components, by offering a solution that converts an analog video source (RGB/YPbPr) for use with a digital HDMI® display.

This versatile analog-digital converter not only supports resolutions up to 1920x1200 including high-definition 1080p, but also enables you to convert and combine an analog RCA audio source into its digital HDMI® output signal.

The VGA2HD2 Component/VGA to HDMI converter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Converting an analog video output signal from a computer for use with an HDTV
- Removing the clutter at the back of a monitor/display, by replacing multiple cables with a single HDMI® cable
- Connect a laptop computer to a boardroom projector or display, for on-screen presentations

Funktioner

- Supports YPbPr (component input) and HD15 PC VGA input
- Supports input resolutions up to 1080p (HDTV) and 1920 x 1200 (PC)
- Includes Component to VGA adapter cable

Hårdvara

Garantipolicy	2 Years
Active or Passive Adapter	Aktiv
AV-ingång	Komponent YCbCr VGA Audio RCA
AV-utgång	HDMI
Audio	Ja

Prestanda

Stödda upplösningar	Maximum of 1080p for HD Input, and 1920x1200 for PC input
Stöd för widescreen	Ja

Kontakt(er)

Connector A	VGA (15-stifts, High Density D-Sub) Stereoaudio (2 x RCA) Komponentvideo (3 x RCA)
Connector B	HDMI (19-stifts)

Särskilda anmärkningar/krav

System- och kabelkrav	HDMI® M/M Cable (Destination) VGA M/M Cable (If using VGA as source)
-----------------------	---

Ström



Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.3A
Utspänning	5 DC
Utström	1.2A
Polaritet på mittpol	Positiv
Kontakttyp	N
Strömförbrukning	6

Miljö

Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-20°C to 60°C (4°F to 140°F)
Luftfuktighet	20~90% RH

Utseende

Färg	Svart
Produktlängd	4.3 in [11 cm]
Produktbredd	3.1 in [78 mm]
Produkthöjd	1.2 in [30 mm]
Produktvikt	6.6 oz [188 g]

Förpackning

Package Length	8.3 in [21 cm]
Package Width	4.5 in [11.5 cm]
Package Height	2.4 in [61 mm]
Fraktvikt (förpackning)	19.1 oz [540 g]

Vad det är i lådan

Ingår i paketet	PC/HD to HDMI Converter with Audio
-----------------	------------------------------------



VGA to Component (RCA) Breakout Cable

Universal Power Adapter (US/UK/EU/AUS)

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

