

Professional VGA to HDMI Audio Video Converter with Scaler

Product ID: VGA2HDMIPRO



The VGA2HDMIPRO VGA to HDMI Audio Video Converter with scaler takes an analog VGA video signal and converts to a digital HDMI or DVI-D output. The device has a built-in scaler that will allow you to adjust the output signal to a resolution that is compatible with your HDMI (or DVI) enabled display. In addition to the video conversion, the device also features both a 3.5 mm and Toslink audio connection providing the option to output the accompanying audio combined into the HDMI output, or through a separate Toslink cable to your television or home theater receiver. A perfect solution for bridging your analog technology with a newer DVI or HDMI-enabled device while maintaining high-quality video and audio performance (up to 1920x1200 / 1080p).

The VGA to HDMI converter/scaler features an automatic native resolution detection feature that make it easy to setup and ensures broad display compatibility as well as a convenient on-screen display menu offering access to several selectable output resolutions and image adjustments giving you full control of your multimedia output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- A simple solution for watching content stored on your computer, on your HDTV display
- Capture an audience's attention at trade shows and retail environments with HD content
- Present information in the clearest possible way, in professional presentations or lectures
- Convert analog video and audio to digital HDMI content

Features

- Supports input resolutions up to 1080p (HDTV) and 1920 x 1200 (PC)
- Supports input of analog audio or digital audio
- HDCP 1.1, and DVI 1.0 compliant
- Automatically detects native resolution of the connected display

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	VGA
	3.5 mm Stereo Audio
	Toslink
AV Output	HDMI
	3.5 mm Stereo Audio
	Toslink
Audio	Yes
Industry Standards	DVI 1.0, HDCP 1.1

Performance

Maximum Analog Resolutions	1920 x 1200
Maximum Digital Resolutions	1920 x 1200
Wide Screen Supported	Yes

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
	3.5 mm Mini-Jack (3 Position)
	Toslink (SPDIF, Optical)
Connector B	HDMI (19 pin)
	Stereo Audio (2 x RCA)



Toslink (SPDIF, Optical)

3.5 mm Mini-Jack (3 Position)

Power

Power Source	AC Adapter Included
Output Voltage	5 DC
Output Current	2.6A
Center Tip Polarity	Positive

Physical Characteristics

Color	Black
Material	Steel
Product Length	4.1 in [10.5 cm]
Product Width	3.0 in [76 mm]
Product Height	1.2 in [30 mm]
Weight of Product	21.6 oz [612 g]

Packaging Information

Package Length	11.0 in [27.9 cm]
Package Width	2.9 in [74 mm]
Package Height	7.2 in [18.4 cm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

What's in the Box

Included in Package	VGA to HDMI Converter / Scaler
	4ft (1.2m) VGA Cable
	6ft (1.8m) 3.5mm to RCA Cable
	Universal Power Adapter (US/UK/EU/AUS)
	Instruction Manual



****Product appearance and specifications are subject to change without notice.***

