

## VGA PC to TV Video Converter with Remote Control

**Product ID:** VGA2NTSCPRO



This High Resolution VGA to TV Video Converter/Scaler accepts your computer's VGA signal and converts the graphics data into TV video format (composite, S-Video, and analog RGB for SCART implementation).

A versatile video solution, the VGA to TV video converter/scaler supports NTSC, PAL and SECAM video systems, acting as a VGA to NTSC/PAL Converter and features adjustable zoom, freeze, horizontal/vertical scaling, picture positioning, brightness, sharpness, and flicker control - allowing you to tweak the video as needed to suit your display.

A practical tool for synchronizing your monitor and television screens, the converter/scaler provides simultaneous display on both TV screen and PC monitor, and features a handy remote control that allows you to make adjustments from a distance.

## Certifications, Reports and Compatibility

### Applications

- Displays computer screen images on your TV
- An inexpensive way to increase the size of a computer display
- Use your TV to display computer presentations, surfing the Internet, playing video games and more
- Great for boardroom meetings, tradeshow and lectures

### Features

- Provides output in both composite and S-Video formats

- True color quality
- Simultaneous display on both TV screen and PC monitor
- Supports NTSC, PAL and SECAM video systems. SECAM systems display by analog RGB output port
- 4 times zoom function support
- Handy remote control allows you to make adjustments from a distance
- Adjustable zoom, freeze, horizontal/vertical scaling, picture positioning, brightness, sharpness, and flicker control

---

#### Hardware

Warranty	2 Years
AV Input	VGA
AV Output	Composite S-Video
Audio	No

---

#### Performance

Maximum Analog Resolutions	1152 x 864
Supported Resolutions	1152x864(=60Hz), 1024x768(=75Hz), 800x600(=85Hz), 640x480(=100Hz)
Frequency Range	Vertical 50Hz - 100Hz Horizontal 25KHz - 58.464KHz

---

#### Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	Composite Video (1 x RCA) S-Video (4 pin, Mini-DIN) VGA (15 pin, High Density D-Sub)

---

#### Power

Power Source	AC Adapter Included
Input Voltage	115V AC



Output Voltage	9V DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M

---

**Physical Characteristics**

Color	Beige
Product Length	6.5 in [16.5 cm]
Product Width	4.1 in [10.5 cm]
Product Height	1.0 in [26 mm]
Weight of Product	7.7 oz [217 g]

---

**Packaging Information**

Package Length	11.8 in [30 cm]
Package Width	2.4 in [60 mm]
Package Height	7.8 in [19.7 cm]
Shipping (Package) Weight	34.6 oz [980 g]

---

**What's in the Box**

Included in Package	VGA to NTSC/PAL Converter w/ Remote
	CR2025 3V Battery
	RCA cable M/M
	VGA cable 15 pin M/F
	4 pin M/M cable
	9V DC Adapter
	Manual

---

*\*Product appearance and specifications are subject to change without notice.*