

VGA to RCA and S-Video Converter - USB Power

Product ID: VGA2VID2



This VGA to RCA/S-Video converter box provides a simple way to convert and scale a 1080p VGA video input signal to a 480i composite (CVBS) or S-Video output signal. Perfect for use with legacy projectors or TV sets.

Equipped with a NTSC/PAL toggle switch and a scan button for simple configuration and selection of your video output settings, this compact VGA to Composite and S-Video adapter installs quickly and easily, for a true plug-and-play experience.

By using this VGA to AV adapter you can connect a PC's VGA connector to legacy TVs and projectors, ultimately saving the costs of upgrading your equipment. It's ideal for boardroom settings, medical imaging and watching videos on your S-Video or Composite display.

The PC to television converter features an integrated video scaler circuit that dynamically converts VGA video input signals with resolutions up to 1920x1200 @ 60Hz. To ensure compatibility with your display or projector the computer to TV converter outputs high quality 640 x 480 video, the highest supported by S-Video or Composite.

VGA2VID2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Great for boardroom meetings, tradeshows, lectures, and CRT digital signage solutions
- An inexpensive way to increase the size of a computer display
- Displays computer screen images on your TV or Projector

Features

- Provides output in both Composite and S-Video formats
- Supports PC input resolutions up to 1920 x 1080
- Select between NTSC and PAL outputs
- Dynamically adjust image underscan and overscan
- Powered by USB port

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	VGA
AV Output	Composite
	S-Video
Audio	No

Performance

Supported Resolutions	Input - Up to 1920x1080 60Hz
	Output - 640x480 60Hz

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	S-Video (4 pin, Mini-DIN)
	Composite Video (1 x RCA)

Power

Power Source	USB-Powered
Plug Type	USB Mini-B (5 pin)
Power Consumption (In Watts)	2.5W

Environmental

Operating Temperature	0 to 50 (32 - 122F)
-----------------------	---------------------



Storage Temperature	-10 to 80 (14 to 176F)
Humidity	5 to 90 % RH

Physical Characteristics

Color	Black
Product Length	2.4 in [60.5 mm]
Product Width	2.1 in [54 mm]
Product Height	0.8 in [20 mm]
Weight of Product	1.6 oz [46 g]

Packaging Information

Package Length	4.1 in [10.5 cm]
Package Width	5.2 in [13.3 cm]
Package Height	0.9 in [24 mm]
Shipping (Package) Weight	5.7 oz [162 g]

What's in the Box

Included in Package	VGA to S-Video and Composite Adapter
	Mini USB Power Cable
	Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

