

1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

Product ID: VGABNCMF1



The VGABNCMF1 1-foot Coax HD15 VGA to 5 BNC RGBHV Adapter Cable features an HD15 VGA (male) connector and 5 BNC (RGBHV) (female) connectors, allowing you to connect your existing BNC video source to a VGA distribution amplifier or PC.

The cable can also be used with a VGA out signal, breaking out to 5 BNC female connectors that can be used with a 5 BNC (M-M) cable for use with a BNC monitor/display.

Certifications, Reports and Compatibility



Applications

- Connect your BNC connected cabled panels and projectors to a VGA distribution amplifier or PC

Features

- Short flexible cable design
- HD15 VGA Male to 5 BNC Female Connectors

Hardware	Warranty	Lifetime
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	CMG Rated (General Purpose)

Connector(s)	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	BNC (RF Coax)
Special Notes / Requirements	Note	RGB signal: Red, Green, Blue wires, Vertical Sync: Black wire, Horizontal Sync: White wire
Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	12.0 in [3.0 cm]
	Cable OD	0.3 in [8.5 mm]
	Product Length	12.0 in [3.0 cm]
	Weight of Product	3.6 oz [103 g]
Packaging Information	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.7 in [17 mm]
	Shipping (Package) Weight	3.8 oz [108 g]
What's in the Box	Included in Package	1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

**Product appearance and specifications are subject to change without notice.*

