

6in Coax High Resolution VGA Port Saver Cable - HD15 M/F

Productcode: VGAEXTAA6IN



The VGAEXTAA6IN 6-inch VGA Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a VGA cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Extend a VGA interface by 6in
- Protect the video card or monitor's VGA port from wear and tear caused by frequent connect/disconnects

Eigenschappen

- Molded connectors with strain relief

Hardware

	Garantiebeleid	Lifetime
	Connectormateriaal	Nikkel
	Type kabelmantel	PVC - Polyvinyl Chloride
	Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Connector(en)	Connector A	1 - VGA (15-polig, D-Sub met hoge dichtheid)
	Connector B	1 - VGA (15-polig, D-Sub met hoge dichtheid)
Fysieke eigenschappen	Kleur	Zwart
	Draaddikte	28 AWG
	Kabellengte	6.0 in [152.4 mm]
	Gewicht product	3.2 oz [90 g]
Verpakkingsinformatie	Verpakkingsaantal	1
	Lengte Verpakking	4.9 in [12.5 cm]
	Package Width	0.7 in [19 mm]
	Package Height	8.5 in [21.5 cm]
	Verzendgewicht (verpakt)	0.2 lb [0.1 kg]
Wat wordt er meegeleverd	Meegeleverd	1 - 6in Coax High Resolution VGA Port Saver Cable
Garantiebepalingen	Warranty	Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.