

6in Coax High Resolution VGA Port Saver Cable - HD15 M/F

Produkt ID: VGAEXTAA6IN



The VGAEXTAA6IN 6-inch VGA Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a VGA cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

Certifikat, rapporter och kompatibilitet

Användning

- Extend a VGA interface by 6in
- Protect the video card or monitor's VGA port from wear and tear caused by frequent connect/disconnects

Funktioner

- Molded connectors with strain relief

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel

Kabelmanteltyp PVC - Polyvinyl Chloride

Brandteknisk klass CMG-klass (General Purpose)

Kontakt(er)

Connector A VGA (15-stifts, High Density D-Sub)

Connector B VGA (15-stifts, High Density D-Sub)

Utseende

Färg Svart

Tråddimension 28 AWG

Kabellängd 6.0 in [15.2 cm]

Produktvikt 3.2 oz [90 g]

Förpackning

Package Length 4.9 in [12.5 cm]

Package Width 0.7 in [19 mm]

Package Height 8.5 in [21.5 cm]

Fraktvikt (förpackning) 3.2 oz [90 g]

Vad det är i lådan

Ingår i paketet 6in Coax High Resolution VGA Port Saver Cable

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

