

6in Coax High Resolution VGA Port Saver Cable - HD15 M/F

**Product ID:** VGAEXTAA6IN



The VGAEXTAA6IN 6-inch VGA Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a VGA cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

## Certifications, Reports and Compatibility

## Applications

- Extend a VGA interface by 6in
- Protect the video card or monitor's VGA port from wear and tear caused by frequent connect/disconnects

## Features

- Molded connectors with strain relief

---

### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)

---

**Connector(s)**

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 in [15.2 cm]
Weight of Product	3.2 oz [90 g]

---

**Packaging Information**

Package Length	4.9 in [12.5 cm]
Package Width	0.7 in [19 mm]
Package Height	8.5 in [21.5 cm]
Shipping (Package) Weight	3.2 oz [90 g]

---

**What's in the Box**

Included in Package	6in Coax High Resolution VGA Port Saver Cable
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

