

Composite en S-Video naar DVI-D Video converter met scaler

Productcode: VID2DVIDTV



This Composite video/S-Video to DVI-D Video Converter/Scaler lets you convert from composite/s-video/YCbCr/RGB resolutions and video formats to DVI-D, automatically detecting the video source input resolution and allowing you to customize the output resolution and refresh rate through an easy to use on-screen-display menu.

Great for home theatre peripherals like DVD players, the Composite video/S-Video to DVI-D Video Converter/Scaler lets you connect non-DVI/HDTV enabled equipment to DVI or HDTV display devices like flat panel monitors, DVI projectors and plasma screen TVs.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Security
- Display video feeds from DVD players, VCRs and more on DVI monitors, plasma displays, DVI input projectors and HDTVs
- Home Theatre
- Educational

- Medical
- Conference Room

Eigenschappen

- Includes a plastic bracket for wall mounts or side panel installation
- Compatible with input from broadcast formats worldwide, including NTSC and PAL
- Includes a memory recall feature that automatically reinstates the setting last used
- A 48 MByte frame buffer eliminates image tear/video hiccupping
- Adjust picture brightness, contrast, color, and RGB levels

Hardware

Garantiebeleid	2 Years
Active or Passive Adapter	Actief
AV-ingang	Composite
	S-Video
	Component
AV-uitgang	DVI
Audio	Nee

Prestaties

Ondersteunde resoluties	HDTV Output(50/60Hz) 1080i, 720p, 576p, 480p PC Output (RGBHV, Progressive Scan) 1280 x 1024, 1280 x 768, 1024 x 768, 800 x 600, 640 x 480
Signaalniveau's	Input Signal Levels: Video @ 1V p-p, 75 ohm Y @ 1 V p-p, 75 ohm Color @ 0.7V p-p, 75 ohm

Connector(en)	Connector A	1 - Composiet video (1 x RCA)
		1 - S-Video (4-polig, Mini-DIN)
	Connector B	1 - DVI-I (29-polig)
Speciale opmerkingen / vereisten	Notitie	Multiple refresh rates supported on PC output - See product manual for full list
Voeding		
	Voedingsbron	Inclusief wisselstroomadapter
	Ingangsspanning	100 - 240 AC
	Uitgangsspanning	5 DC
	Uitgangsstroom	2.6A
	Polariteit pin midden	Positief
	Vermogensopname	13
Fysieke eigenschappen		
	Kleur	Zwart
	Lengte product	5.7 in [14.6 cm]
	Breedte product	3.0 in [7.7 cm]
	Hoogte product	1.2 in [3 cm]
	Gewicht product	9.9 oz [280 g]
Verpakkingsinformatie		
	Verpakkingsaantal	1
	Lengte Verpakking	11.1 in [28.3 cm]
	Package Width	2.8 in [72 mm]
	Package Height	7.3 in [18.6 cm]

	Verzendgewicht (verpakt)	2.4 lb [1.1 kg]
Wat wordt er meegeleverd	Meegeleverd	1 - Video to DVI/HDTV Scaler
		1 - Plastic Bracket
		1 - 3 foot (1 meter) Composite RCA cable
		1 - YCbCr RCA to 8 pin DIN adapter
		1 - 6 foot (1.8 meter) DVI-D DVI cable M-M
		1 - Wall-mount power adapter
		1 - User's manual
Garantiebepalingen		
	Warranty	2 Jaar

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.